

MANUAL GAS CONTROL

# THERMOELECTRIC SAFETY DEVICE

SIDE OUTLET OR, ALTERNATIVELY (series B3), ADDITIONAL PILOT OUTLET



g

r

0

U

р

.

i t

S

i t


W

W

W



# MULTIFUNCTIONAL MANUAL CONTROL



Manual control with thermoelectric safety device. Model 420 B3 has a gas outlet for connection to the pilot burner. Versions are available for working temperatures up to 150°C and pressures up to 5 bar.

400 M1 and 420 B3 are suitable for use with heaters, ovens, barbecues and fireplaces.

### MAIN FEATURES

Brass body. Connection with thermocouple M8x1 (M9x1 on request). Threading under the button (optional). Pilot outlet (series B3). Gas inlet and outlet coaxial or at different heights.

# TECHNICAL DATA

- Gas connections:
- Installation position:
- Gas families:
- Maximum gas inlet pressure:
- Working temperature range:

Rp 1/4 ISO 7 (1/8 or 3/8 on request) any position I, II and III series M1: 150 mbar series B3: 50 mbar (on request: series M1: 5 bar series B3: 3 bar) 0...80°C (0...150°C on request)

Data refer to EN 125 standards

2

### **OPERATION**

### Ignition

Depress the button and ignite the main burner (in series M1) or the pilot burner (in series B3) at the same time, keeping the button fully depressed for a few seconds (fig. 1).

Release the button (fig. 2) and check that the pilot flame stays on. If it goes out, repeat the ignition operations.

#### Shutdown

Close the gas cock to turn off the main burner.

**CAUTION:** if, after releasing the button, the burner goes off, wait about one minute before repeating the operation.





# INSTALLATION

#### Main gas connection

The connection is made using gas pipes with threading in accordance with the dimensional specifications of the gas inlet and outlet.

#### **Connection to the pilot burner (series B3)**

Pipes with 4 mm, 6 mm and 1/4 can be used Use a nut and olive of appropriate dimensions. Tighten to 7 Nm torque.

Implement the provisions in the Use and Maintenance manual - code 9.956.400 - for installation, adjustment and use.

### FLOW RATE AS A FUNCTION OF PRESSURE DROP

M1 - 1/8" x 1/8"			
I	Family (d = 0.45)	Q = 1.3 m <sup>3</sup> /h	$\Delta p = 5 \text{ mbar}$
	Family (d = 0.6)	Q = 1.1 m <sup>3</sup> /h	$\Delta p = 5 \text{ mbar}$
	Family (d = 1.7)	Q = 1.3 kg/h	$\Delta p = 5 \text{ mbar}$

M1 - 3/8" x 3/8"					
I Family (d = 0.45)		$Q = 2.5 \text{ m}^{3}/\text{h}$	$\Delta p = 5 \text{ mbar}$		
II	Family (d = 0.6)	Q = 2.2 m <sup>3</sup> /h	$\Delta p = 5 \text{ mbar}$		
Ш	Family (d = 1.7)	Q = 2.7 kg/h	∆p = 5 mbar		


	B3		
I	Family (d = 0.45)	Q = 2.1 m <sup>3</sup> /h	$\Delta p = 5 \text{ mbar}$
Ш	Family (d = 0.6)	Q = 1.8 m <sup>3</sup> /h	$\Delta p = 5 \text{ mbar}$
Ш	Family (d = 1.7)	Q = 2.1 kg/h	$\Delta p = 5 \text{ mbar}$

<i>B3 - 3/8" x 3/8"</i>						
I	Family (d = 0.45)	Q = 3.4 m <sup>3</sup> /h	$\Delta p = 5 \text{ mbar}$			
Ш	Family (d = 0.6)	Q = 3.0 m <sup>3</sup> /h	$\Delta p = 5 \text{ mbar}$			
III	Family (d = 1.7)	Q = 3.8 kg/h	$\Delta p = 5 \text{ mbar}$			


### DESCRIPTION

- 1 Ignition button
- 2 Thermocouple connection
- 3 Gas inlet
- 4 Gas outlet

- 5 Inlet and outlet at 90 degrees
- 6 Pilot outlet (series B3)
- 7 Inlet and outlet in line, at different heights









(B3)

(420 B3: inlet and outlet at 90 degrees)

(400 M1: inlet and outlet at different heights)

### DIMENSIONS







16,8

26,5

59,2







02,5

49,2

### **SIT La Precisa S.p.A.** Viale dell'Industria 31-33

Tel. +39/049.829.31.11, Fax +39/049.807.00.93 www.sitgroup.it - e-mail: mkt@sitgroup.it